



Fraunhofer

TESTED[®]
DEVICE

Gimatic s.r.l.
Parallel gripper MPLM2535
Report No. GI 2510-1678

DUPLICATE

Statement of
Qualification

Single product
Particle Emission
in Cleanroom
(atmospheric)

Customer	Gimatic s.r.l. Via Enzo Ferrari 2/4 25030 Roncadelle (BS) Italy
Tested product	
Category:	Automation Components
Subcategory:	Positioning Systems
Product name:	Long stroke parallel gripper MPLM2535 (manufacturing date: 7/21/2025; color: black; batch number: ODL-AE12556)

Random sampling of particle emissions (airborne) at representative sites in cleanroom under atmospheric conditions

Standards/guidelines:	ISO 14644-1, -14 The norms stated generally refer to the version valid at the time of the tests.
Test equipment:	Optical particle counter: LasAir II 110 and LasAir III 110 with measuring ranges $\geq 0.1\text{ }\mu\text{m}$, $\geq 0.2\text{ }\mu\text{m}$, $\geq 0.3\text{ }\mu\text{m}$, $\geq 0.5\text{ }\mu\text{m}$, $\geq 1.0\text{ }\mu\text{m}$ and $\geq 5.0\text{ }\mu\text{m}$
Test environment parameters:	- Cleanroom Air Cleanliness Class (according to ISO 14644-1):..... ISO 1 - Airflow velocity:.....0.45 m/s - Airflow pattern:..... vertical laminar flow - Room temperature:22 °C ± 0.5 °C - Relative humidity: 45 % ± 5 %
Test procedure parameters:	- Control unit:.....supplied by customer - Installation position:..... vertical - Cycle time: t = 2.0 s (1.0 s for opening; 1.0 s for closing) - Working gripper time per cycle:..... 1.06 s - Load:..... none

Test result / Classification	The long stroke parallel gripper MPLM2535 is suitable for use under the specified test parameters (room temperature: 22 °C ± 0.5 °C; relative humidity: 45 % ± 5 %) in cleanrooms of the following Air Cleanliness Classes according to ISO 14644-1:
------------------------------	--

Test parameter(s)	Air Cleanlines Class
Installation position: vertical Cycle time: 2.0 s (1.0 s for opening; 1.0 s for closing) Working gripper time per cycle: 1.06 s Load: none	5
Overall result	

Please note: Transport damages, incorrect installation, oil leakage, aging behavior, corrosion etc. can influence the test result.

The measuring devices used for the qualification tests are calibrated at regular intervals; their results can be traced back to national and international standards. In cases where no national standards exist, the test procedure implemented complies with the technical regulations and norms applicable at the time of the test. The relevant documentation can be viewed on request at any time.

Detailed information and parameters of the test environment can be found in the Fraunhofer IPA test report.

Fraunhofer Institute for Manufacturing Engineering and Automation IPA	GI 2003-1164 Report No. first document	Stuttgart, October 20, 2020 Place, date of first document issued
Business unit Testing and Certification	GI 2510-1678 Report No. current document	Stuttgart, October 24, 2025 Place, current date
Nobelstrasse 12 70569 Stuttgart Germany	on behalf of Dr.-Ing. Frank Bürger, head of business unit Testing and Certification	